

Warning!

Please read the user manual included in this work as it contains important information related with safety of installation and use of the device.

Only persons who read the user manual may use the device.

The user manual must be kept because it may be required in the future. The device is to be used exclusively for purposes specified in this user manual.

The device must be unpacked prior to starting-up. After removing the packaging make sure the device is in working order. If the product has defects, it should not be used until it is repaired.

The product is intended for use at home and commercial use and may not be used for other than intended use.

The manufacturer is not liable for damages resulting from not adhering to the rules contained in the user manual, therefore, we recommend to follow the aforementioned safety rules for operation and maintenance of the device. In this way you will ensure yourself safety and avoid causing damage to the device.

The manufacturer and the supplier are not liable for losses or damages arising out of the product, including financial or intangible losses, loss of profits, income, data, pleasure from use of the product or other products related with it - indirect, incidental or consequential loss or damage. The above provisions apply whether the loss or damage concerns:

1. Deterioration of quality or the lack of operation of the products or products related with it due to damage as well as the lack of access to the product when it is undergoing repair, which results in stoppage the loss of user's time or a break in business activity; 2. Improper results of operation of the product or products related with it;

3. It applies to losses and damages according to any legal category, including negligence and other losses, termination of a contract, expressed or implied guarantee and strict liability (even if the manufacturer or the supplier was notified about the possibility of occurrence of such damages).

Safety measures:

Particular attention at designing was directed to quality standards of the device where ensuring safety of operation is the most important factor.

The device must be secured against contact with caustic, staining and viscous fluids.

The device was designed in such a way that it restarts operation when power supply is restored after a break.

Attention! We recommend using protections to further protect the device from possible overvoltages in installations. Surge protectors are effective protection against accidental pass to the device voltages higher than the rated. Damages caused by pass the voltages higher than specified in manual, are not under warranty.

Turn off the device before transporting it.

Prior to connecting the device to a power source check whether the supplied voltage is consistent with rated voltage specified in the user manual.

Proper product disposal:

A marking of a crossed out waste bin indicates that the product may not be disposed together with other household waste in the entire EU. To avoid possible damage to the natural environment of health due to uncontrolled waste disposal, therefore, it should be handed over for recycling, propagating in this way sustainable use of natural resources.

To return a worn-out product, use a collection and disposal system of this type of equipment or contact a seller from whom it was purchased. He will then be recycled in an environmentally-friendly way.





IP camera with efficient H.264 / H.265 image compression algorithm for clear and smooth video streaming at maximal resolution of 5 MPx.

PoE powering possibility, compatible with the 802.3af standard makes the device more universal and easier to install. The range of IR illumination according to the manufacturer data, depends on outer conditions (visibility - air transparency, environment, wall colors ie. scene reflectance).

The camera has extensive functions of intelligent image analysis.



Standard:	ТСР/ІР		
Sensor:	1/2.7 " Progressive Scan CMOS		
Matrix size:	5 Mpx		
Resolution:	2960 x 1668 - 5 Mpx, 2880 x 1620 - 4.7 Mpx, 2688 x 1520 - 4 Mpx, 2560 x 1440 - 3.7 Mpx, 2048 x 1536 - 3 Mpx, 2304 x 1296 - 3 Mpx, 1920 x 1080 - 1080p, 1280 x 960 - 1.3 Mpx, 1280 x 720 - 720p		
Lens:	2.8 mm		
View angle:	 97 ° (manufacturer data) 107 ° (our tests result) 		
Range of IR illumination:	50 m		
Memory card slot:	Micro SD memory cards up to 256GB support (possible local recording)		
Image compression method:	AI H.265 / H.265+ / H.265 / AI H.264 / H.264+ / H.264 / H.264H / H.264B / MJPEG		
Alarm inputs / outputs:	-		
Audio:	 Microphone built-in Noise reduction Audio detection 		



DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60



Main stream frame rate:	• 20 fps @ 5 Mpx, • 25 fps @ 4 Mpx			
Network interface:	10/100 Base-T (RJ-45)			
Network protocols:	IPv4/IPv6, HTTP, TCP, UDP, ARP, RTP, RTSP, RTCP, RTMP, SMTP, FTP, SFTP, DHCP, DNS, DDNS, QoS, UPnP, NTP, Multicast, ICMP, IGMP, NFS, SAMBA, PPPoE SNMP			
WEB Server:	Built-in			
Max. number of on-line users:	20			
ONVIF:	21.12			
Main features:	 WDR - 120 dB - Wide Dynamic Range 3D-DNR - Digital Noise Reduction F-DNR (Defog) - Reduction of image noise caused by precipitation ROI - improve the quality of selected parts of image NAS - Network Attached Storage support BLC/HLC - Back Light / High Light Compensation Possibility to change the resolution, quality and bit rate ICR - Movable InfraRed filter Day/Night mode (color/b&w/auto) Auto White Balance AGC - Automatic Gain Control Mirror - Mirror image Motion Detection Configurable Privacy Zones AFSA - Anti-flicker Self-adaption - The technology eliminates the tiring eyes flickering image effect AI SSA AI Smart Scene Adaptive - scene auto-adaptation using deep learning algorithms to detect environmental conditions such as rain, fog, backlight, low light and flickering, in order to set the optimal image parameters SMD 4.0 - searching for an object classified as: human, motor vehicle - increased detection distance and resistance to false alarms Quick Pick - AI technology enabling, together with the recorder, quick identification of interesting objects (people/vehicles) based on an artificial intelligence algorithm. It allows to extract and compare the colors of clothes and vehicles IVS analysis : crossing the line (tripwire), intrusion - classification of people and vehicles, scene changing, video tampering 			
Mobile phones support:	Port no.: 37777 or access by a cloud (P2P) • Android: Free application <u>DMSS</u> • iOS (iPhone): Free application <u>DMSS</u>			
Default IP address:	192.168.1.108			
Default admin user / password:	admin / - The administrator password should be set at the first start			
Web browser access ports:	80, 37777			
PC client access ports:	37777			
Mobile client access ports:	37777			
Port ONVIF:	80			
RTSP URL:	rtsp://admin:hasło@192.168.1.108:554/cam/realmonitor?channel=1&subtype=0 - Main stream rtsp://admin:hasło@192.168.1.108:554/cam/realmonitor?channel=1&subtype=1 - Sub stream			
Power supply:	• PoE (802.3af), • 12 V DC / 630 mA			





Power consumption:	• \leq 7.6 W @ 12 V DC • \leq 8.9 W @ PoE		
Housing:	Dome - Metal		
Color:	Black		
"Index of Protection":	IP67		
Operation temp:	-40 °C 60 °C		
Weight:	0.53 kg		
Dimensions:	Ø 106 x 94 mm		
Supported languages:	Polish, English, Czech, French, Spanish, Dutch, German, Portuguese, Russian, Romanian, Turkish, Ukrainian, Hungarian, Italian		
Manufacturer / Brand:	DAHUA		
Guarantee:	3 years		

Camera is out from clamping ring:



Memory card slot and "Reset" button:







Mounting dimensions:



See how to initialize DAHUA cameras:

In the kit:

:







Example captures of device interface:









DELTA-OPTI Monika Matysiak; https://www.delta.poznan.pl POL; 60-713 Poznań; Graniczna 10 e-mail: delta-opti@delta.poznan.pl; tel: +(48) 61 864 69 60



14	Telepise Interception Interception Interception Comparison Compari					
		Post I	Edited.			
		The st	14	fordedeel V		
		Report.	Annual I	+ 0		
		Podewith HR	Sector 1			
		Tracing.	Neurosci			
		Large	Detroit			
		Tone Ingh	(area			
			band	e		
			1941	09		
			1.000			
	transinisipina assempt					
	Tables Repetit Seadler					

PACKAGE

Dimensions (L x W x H): 0x0x0 mm	Gross Weight: 0 kg
----------------------------------	--------------------

